

| <b>1.</b><br>Device Name              | <b>NITE LONG</b>   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
|---------------------------------------|--|--------------------------------------|------------------------------------|-----------------|---------------------------|-------------|----------------|--------------------------------------|------------------------------------|-----------------|---------------------------|------------------------|------------|------------|---------------|----------------|-------|--------|---------------|----------------|--------|------|---------------|----------------|-------|--------|---------------|----------------|---|----|-------|--------|--------|-------|-----|-----|-------|--------|--------|-------|-----|
| <b>2.</b><br>Description              | Powder free nitrile, Extra Long Beaded Cuff, On-Line Chlorinated, Ambidextrous, Non Sterile, Textured Surface, Free from Vinyl, BPA, Phthalates and MBT.   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>3.</b><br>Product Codes & Sizes    | <table border="1"> <thead> <tr> <th>Product Code</th> <th>Size</th> <th>Inner Barcode</th> <th>Shipper Barcode</th> </tr> </thead> <tbody> <tr> <td>41092</td> <td>SMALL</td> <td>9311059410926</td> <td>19311059410923</td> </tr> <tr> <td>41093</td> <td>MEDIUM</td> <td>9311059410933</td> <td>19311059410930</td> </tr> <tr> <td>41094</td> <td>LARGE</td> <td>9311059410940</td> <td>19311059410947</td> </tr> <tr> <td>41095</td> <td>XL</td> <td>9311059410957</td> <td>19311059410954</td> </tr> <tr> <td>41096</td> <td>XXL</td> <td>9311059410964</td> <td>19311059410961</td> </tr> </tbody> </table>   |                                      |                                    |                 | Product Code              | Size        | Inner Barcode  | Shipper Barcode                      | 41092                              | SMALL           | 9311059410926             | 19311059410923         | 41093      | MEDIUM     | 9311059410933 | 19311059410930 | 41094 | LARGE  | 9311059410940 | 19311059410947 | 41095  | XL   | 9311059410957 | 19311059410954 | 41096 | XXL    | 9311059410964 | 19311059410961 |  |    |       |        |        |       |     |     |       |        |        |       |     |
| Product Code                          | Size   | Inner Barcode                        | Shipper Barcode                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| 41092                                 | SMALL  | 9311059410926                        | 19311059410923                     |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| 41093                                 | MEDIUM   | 9311059410933                        | 19311059410930                     |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| 41094                                 | LARGE  | 9311059410940                        | 19311059410947                     |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| 41095                                 | XL   | 9311059410957                        | 19311059410954                     |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| 41096                                 | XXL  | 9311059410964                        | 19311059410961                     |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>4.</b><br>Recommended Applications | <ul style="list-style-type: none"> <li>Medical</li> <li>Dental</li> <li>Hospitals</li> <li>Diagnostic</li> <li>Pharmaceutical</li> <li>Laboratory</li> <li>Hair and Beauty</li> <li>Aged Care</li> <li>Childcare</li> <li>Tattooists</li> <li>Food Service</li> <li>Emergency Services</li> <li>Abattoirs &amp; Meatworks</li> <li>Agriculture</li> <li>Milking</li> <li>Veterinary</li> </ul>   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>5.</b><br>Materials                | Nitrile, SDBS Surfactant, Potassium Hydroxide, Ammonia Solution, Sulphur, Zinc Oxide, Titanium Dioxide, ZDBC, ZDEC, Calcium Carbonate, Defoamer, Blue Pigment.   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>6.</b><br>Production Process       | Former cleaning and washing, coagulant dipping, coagulant drying, nitrile dipping, nitrile drying oven, beading, leaching tank dip, main curing oven, cooling tank, chlorination tank, soak rinse tank, neutralizer, post leaching tank, blower, stripping, QC inspection, tumbling, packing, Pre-shipment inspection.   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>7.</b><br>Standards & Approvals    | <div style="display: flex; align-items: center;"> <div style="margin-right: 20px;">  </div> <div style="margin-right: 20px;">  </div> <div style="margin-right: 20px;">  </div> <div> <p><b>Nite Long</b> is tested to and complies with;</p> <ul style="list-style-type: none"> <li>ASTM D6319-10</li> <li>Certified under HACCP Food Safety Accreditation</li> <li>Entered into the ARTG - ARTG# 277970</li> <li>Acceptable Quality Level AQL1.5</li> </ul> </div> </div>   |                                      |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>8.</b><br>Dimensions               | <table border="1"> <thead> <tr> <th>SIZE</th> <th>LENGTH (+/-10)</th> <th>THICKNESS FINGER SINGLE WALL +/-0.02</th> <th>THICKNESS PALM SINGLE WALL +/-0.02</th> <th>PALM WIDTH +/-3</th> <th>WEIGHT PER PIECE +/-0.2gm</th> </tr> </thead> <tbody> <tr> <td>SMALL</td> <td>300mm</td> <td>0.15mm</td> <td>0.14mm</td> <td>84mm</td> <td>5.6</td> </tr> <tr> <td>MEDIUM</td> <td>300mm</td> <td>0.15mm</td> <td>0.14mm</td> <td>94mm</td> <td>6.2</td> </tr> <tr> <td>LARGE</td> <td>300mm</td> <td>0.15mm</td> <td>0.14mm</td> <td>105mm</td> <td>6.7</td> </tr> <tr> <td>XL</td> <td>300mm</td> <td>0.15mm</td> <td>0.14mm</td> <td>113mm</td> <td>7.3</td> </tr> <tr> <td>XXL</td> <td>300mm</td> <td>0.15mm</td> <td>0.14mm</td> <td>123mm</td> <td>8.3</td> </tr> </tbody> </table> <p><i>Note: if Textured gloves then minimum requirements shall be 10% lower than those shown in table.</i></p> |                                      |                                    |                 |                           | SIZE        | LENGTH (+/-10) | THICKNESS FINGER SINGLE WALL +/-0.02 | THICKNESS PALM SINGLE WALL +/-0.02 | PALM WIDTH +/-3 | WEIGHT PER PIECE +/-0.2gm | SMALL                  | 300mm      | 0.15mm     | 0.14mm        | 84mm           | 5.6   | MEDIUM | 300mm         | 0.15mm         | 0.14mm | 94mm | 6.2           | LARGE          | 300mm | 0.15mm | 0.14mm        | 105mm          | 6.7   | XL | 300mm | 0.15mm | 0.14mm | 113mm | 7.3 | XXL | 300mm | 0.15mm | 0.14mm | 123mm | 8.3 |
| SIZE                                  | LENGTH (+/-10)   | THICKNESS FINGER SINGLE WALL +/-0.02 | THICKNESS PALM SINGLE WALL +/-0.02 | PALM WIDTH +/-3 | WEIGHT PER PIECE +/-0.2gm |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| SMALL                                 | 300mm  | 0.15mm                               | 0.14mm                             | 84mm            | 5.6                       |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| MEDIUM                                | 300mm  | 0.15mm                               | 0.14mm                             | 94mm            | 6.2                       |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| LARGE                                 | 300mm  | 0.15mm                               | 0.14mm                             | 105mm           | 6.7                       |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| XL                                    | 300mm  | 0.15mm                               | 0.14mm                             | 113mm           | 7.3                       |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| XXL                                   | 300mm  | 0.15mm                               | 0.14mm                             | 123mm           | 8.3                       |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| <b>9.</b><br>Physical Properties      | <table border="1"> <thead> <tr> <th>DESCRIPTION</th> <th>BEFORE AGEING</th> <th>AFTER AGEING</th> </tr> </thead> <tbody> <tr> <td>Elongation at break (%)</td> <td>500 minimum</td> <td>400 minimum</td> </tr> <tr> <td>Tensile Strength (MPa)</td> <td>14 minimum</td> <td>14 minimum</td> </tr> </tbody> </table>  |                                      |                                    |                 |                           | DESCRIPTION | BEFORE AGEING  | AFTER AGEING                         | Elongation at break (%)            | 500 minimum     | 400 minimum               | Tensile Strength (MPa) | 14 minimum | 14 minimum |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| DESCRIPTION                           | BEFORE AGEING  | AFTER AGEING                         |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| Elongation at break (%)               | 500 minimum  | 400 minimum                          |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |
| Tensile Strength (MPa)                | 14 minimum   | 14 minimum                           |                                    |                 |                           |             |                |                                      |                                    |                 |                           |                        |            |            |               |                |       |        |               |                |        |      |               |                |       |        |               |                |   |    |       |        |        |       |     |     |       |        |        |       |     |



| <b>10.</b><br>Colour   | Light Blue   |                          |                                      |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
|--|--|--------------------------|--------------------------------------|--------------------------|--------------------|-------------------|-------|-----|---------------|---------------------|-----|--------|---------------|----------------|-----|-----|---------------|-----------------------------------|-----|------------|------------------------|--|----------------|------------------|---------------------|---------------------|-----|-----|--------------------------------------|-----|------|
| <b>11.</b><br>Performance Requirements                                   | <p>Gloves shall be sampled and inspected in accordance with ISO 2859-1. The inspection levels and acceptable quality limits (AQLs) shall conform to those listed in below table for the characteristics listed.</p> <table border="1" data-bbox="204 405 1567 936"> <thead> <tr> <th>CHARACTERISTICS</th> <th>INSPECTION LEVEL</th> <th>ACCEPTABLE QUALITY LEVEL</th> <th>REFERENCE STANDARD</th> </tr> </thead> <tbody> <tr> <td>Dimensions</td> <td>S2</td> <td>4.0</td> <td>ASTM D6319-10</td> </tr> <tr> <td>Physical Properties</td> <td>S2</td> <td>4.0</td> <td>ASTM D6319-10</td> </tr> <tr> <td>Watertightness</td> <td>G1</td> <td>1.5</td> <td>ASTM D6319-10</td> </tr> <tr> <td>Visual Defects:<br/>Major<br/>Minor</td> <td>G1</td> <td>2.5<br/>4.0</td> <td>Manufacturers Practice</td> </tr> <tr> <td>Packaging Defects<br/>Regulatory<br/>Visual<br/>Critical (Incl Glove Count)</td> <td>G1<br/>G1<br/>S2</td> <td>**<br/>4.0<br/>4.0</td> <td>In House Inspection</td> </tr> <tr> <td>Powder Free Residue</td> <td>N=5</td> <td>-</td> <td>ASTM D6319-10<br/>ASTM D6124-06(2011)</td> </tr> </tbody> </table> <p>Notes: ** indicates unacceptable at any level For Dimensions and Physical Properties a median of 13 test pieces used as per EN455-02-00</p> | CHARACTERISTICS          | INSPECTION LEVEL                     | ACCEPTABLE QUALITY LEVEL | REFERENCE STANDARD | Dimensions        | S2    | 4.0 | ASTM D6319-10 | Physical Properties | S2  | 4.0    | ASTM D6319-10 | Watertightness | G1  | 1.5 | ASTM D6319-10 | Visual Defects:<br>Major<br>Minor | G1  | 2.5<br>4.0 | Manufacturers Practice | Packaging Defects<br>Regulatory<br>Visual<br>Critical (Incl Glove Count) | G1<br>G1<br>S2 | **<br>4.0<br>4.0 | In House Inspection | Powder Free Residue | N=5 | -   | ASTM D6319-10<br>ASTM D6124-06(2011) |     |      |
| CHARACTERISTICS  | INSPECTION LEVEL   | ACCEPTABLE QUALITY LEVEL | REFERENCE STANDARD                   |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Dimensions   | S2   | 4.0                      | ASTM D6319-10                        |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Physical Properties  | S2   | 4.0                      | ASTM D6319-10                        |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Watertightness   | G1   | 1.5                      | ASTM D6319-10                        |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Visual Defects:<br>Major<br>Minor  | G1   | 2.5<br>4.0               | Manufacturers Practice               |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Packaging Defects<br>Regulatory<br>Visual<br>Critical (Incl Glove Count) | G1<br>G1<br>S2   | **<br>4.0<br>4.0         | In House Inspection                  |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| Powder Free Residue  | N=5  | -                        | ASTM D6319-10<br>ASTM D6124-06(2011) |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| <b>12.</b><br>Quality Control Inspection Procedures                      | <ol style="list-style-type: none"> <li>Shipment is placed in quarantine area separately from other gloves in warehouse as one lot</li> <li>Shipment is then sorted by sizes if shipment consists of more than one size.</li> <li>QC inspector records lot number(s) indicted on inner boxes and outer cases, sizes quantity of shipment, buyer, date, etc</li> <li>QC inspector selects at random samples according to ISO procedures for sampling, each lots of different sizes are handled separately</li> <li>Samples are sent for testing as per requirements</li> <li>Results of tests will be recorded and only those that meet acceptance criteria are released for dispatch. If shipment consists of more than one size, shipment will be released only when all lots of different sizes have passed.</li> <li>If a shipment is found to fail test requirements it will be rejected by QC inspector and not released for shipment.</li> </ol>  |                          |                                      |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| <b>13.</b><br>Packaging  | <p>100 pieces will be packed into a dispenser box.<br/>The number contained in each dispenser box determined by count. 10 dispenser boxes are packed in 2 layers of 5 giving 10 dispenser boxes inside export quality shipper carton (outer).</p>  |                          |                                      |                          |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| <b>14.</b><br>Shipper Carton Specifications                              | <table border="1" data-bbox="204 1697 890 2020"> <thead> <tr> <th>SIZE</th> <th>LENGTH (mm)</th> <th>WIDTH (mm)</th> <th>HEIGHT (mm)</th> <th>GROSS WEIGHT (kg)</th> </tr> </thead> <tbody> <tr> <td>SMALL</td> <td>365</td> <td>260</td> <td>270</td> <td>8.4</td> </tr> <tr> <td>MEDIUM</td> <td>365</td> <td>260</td> <td>270</td> <td>8.8</td> </tr> <tr> <td>LARGE</td> <td>365</td> <td>260</td> <td>270</td> <td>9.3</td> </tr> <tr> <td>XL</td> <td>365</td> <td>260</td> <td>270</td> <td>10.3</td> </tr> <tr> <td>XXL</td> <td>365</td> <td>260</td> <td>270</td> <td>10.9</td> </tr> </tbody> </table>  | SIZE                     | LENGTH (mm)                          | WIDTH (mm)               | HEIGHT (mm)        | GROSS WEIGHT (kg) | SMALL | 365 | 260           | 270                 | 8.4 | MEDIUM | 365           | 260            | 270 | 8.8 | LARGE         | 365                               | 260 | 270        | 9.3                    | XL   | 365            | 260              | 270                 | 10.3                | XXL | 365 | 260                                  | 270 | 10.9 |
| SIZE   | LENGTH (mm)  | WIDTH (mm)               | HEIGHT (mm)                          | GROSS WEIGHT (kg)        |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| SMALL  | 365  | 260                      | 270                                  | 8.4                      |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| MEDIUM   | 365  | 260                      | 270                                  | 8.8                      |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| LARGE  | 365  | 260                      | 270                                  | 9.3                      |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| XL   | 365  | 260                      | 270                                  | 10.3                     |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |
| XXL  | 365  | 260                      | 270                                  | 10.9                     |                    |                   |       |     |               |                     |     |        |               |                |     |     |               |                                   |     |            |                        |  |                |                  |                     |                     |     |     |                                      |     |      |



# Nite Long

## Powder Free Extra Long Nitrile Examination Gloves

- 15. Storage Conditions** The gloves will maintain their properties when stored in dry conditions out of direct sunlight at between 10°C to 30°C.
- 
- 16. Shelf Life** The gloves shall have a shelf life of 5 years from the date of manufacture when stored in compliance with the above storage conditions.

